


# Handling module HSW-10-AP-W

Part number: 540225

FESTO

Pick & Place for repositioning parts at an angle of 90°, with additional rest position.



## Data sheet

Feature	Value
Working stroke	9 ... 15 mm
Size	10
Max. linear stroke at 90° swivel angle	90/90 mm
Maximum Z-stroke, wait position	10 mm
Z stroke	80 ... 100 mm
Cushioning	CC: Shock absorber at both ends Soft characteristic
Assembly position	Any
Design structure	linear guide plus rotating bearing Swivel actuator guided motion sequence
Position detection	For proximity sensor
Operating pressure	4 ... 8 bar
Minimum cycle time	0.6 s
Repetition accuracy, end positions	+/-0,02 mm
Operating medium	Compressed air, filtered, unlubricated Filtered, lubricated air
Ambient temperature	0 ... 60 °C
Max. torque Mx	0.6 Nm
Max. torque My	0.6 Nm
Max. torque Mz	0.6 Nm
Maximum process force in Y direction	30 N
Theoretical force at 6 bar	30 N
Product weight	1,350 g
Mounting type	With through-hole and centering sleeve
Pneumatic connection, wait position	M3
Pneumatic connection	M3
Material information, stops	High alloy steel
Material information, spring pressure piece	High alloy steel
Materials information for subbase	Wrought Aluminum alloy Anodized
Material information, holder	Wrought Aluminum alloy Anodized
Materials information for cross-guide	Heat-treatment steel
Material information, swivel lever	Case-hardened steel Burnished
Material information, slotted guide plate	Case-hardened steel Hardened
Material information, sensor rail	Wrought Aluminum alloy Anodized
Material information, ridge	Wrought Aluminum alloy Anodized
Material information, adjusting screw	High alloy steel