


Ball valve

VAPB-3/8-F-63-F0304-CR

Part number: 542844

FESTO

Corrosion and acid resistant



Data sheet

Feature	Value
Design structure	2-way ball valve
Type of actuation	mechanical
Sealing principle	soft
Mounting type	Line installation
Process valve connection	Rp3/8
Flange hole pattern	F03 F04
Inside diameter	12 mm
Nominal diameter DN	10
Nominal pressure of process valve	63
Actuation torque	7 Nm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-:::] Inert gases Water Neutral fluids
Medium temperature	-10 ... 180 °C
Flow rate Kv	10 m ³ /h
Materials information, housing	High alloy steel, non-corrosive
Material number for housing	1.4408
Materials information for seals	FPM PTFE
Material information, globe	High alloy steel, non-corrosive
Material number for ball	1.4401
Materials information for shaft	High alloy steel, non-corrosive
Material number for shaft	1.4401
Product weight	200 g
CE symbol (see declaration of conformity)	according to EU printing device guideline
Corrosion resistance classification CRC	3