



# Electro-cylinder EPCC-BS-60-

Part number: 5428914

FESTO



Exemplary representation



## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	60
Stroke	25 ... 500 mm
Stroke reserve	0 mm
Piston rod thread	M12x1,25
Reversing backlash	100 µm
Spindle diameter	12 mm
Spindle pitch	5 ... 12 mm/U
Max. angular deflection of piston rod +/-	1 deg
Assembly position	Any
Piston-rod end	Male thread Female thread
Motor type	Stepper motor Servomotor
Position detection	For proximity sensor
Design structure	Electric cylinder With ball screw
Spindle type	Ball screw
Protection against torque/guide	with plain-bearing guide
Max. acceleration	5 ... 15 m/s <sup>2</sup>
Max. speed	0.067 ... 0.6 m/s
Repetition accuracy	±0,02 mm
Duty cycle	100 %
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 9
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 95 % non-condensing
Protection class	IP40
Ambient temperature	0 ... 60 °C
Impact energy in end positions	0.024 J
Max. torque Mx	0 Nm
Max. torque My	6.4 Nm
Max. torque Mz	6.4 Nm
Max. radial force at drive shaft	230 N
Max. feed force Fx	1,000 N
Reference value for working load, horizontal	120 kg
Reference value for working load, vertical	60 kg
Mass moment of inertia JH per meter of stroke	0.1195 ... 0.1519 kgcm <sup>2</sup>
Mass moment of inertia JL per kg of working load	0.0063 ... 0.0365 kgcm <sup>2</sup>
Mass moment of inertia, J0	0.0682 ... 0.0779 kgcm <sup>2</sup>
Moving mass with 0 mm stroke	305 g
Additional mass factor per 10 mm of stroke	6.5 g

Feature	Value
Basic weight for 0 mm stroke	1,114 g
Additional weight per 10 mm stroke	69 g
Mounting type	with internal (female) thread with accessories
Materials note	Conforms to RoHS
Material housing	Wrought Aluminum alloy Smooth anodized
Material piston rod	High alloy steel, non-corrosive
Material spindle nut	Steel
Material spindle	Roller bearing steel