


Adding counter CCES-P-C8-E

Part number: 549403

FESTO



Data sheet

Feature	Value
Design structure	Electrical adding counter with battery
Type of reset	Pushbutton or electrical signal
Display	8-digit
Max. counting rate	7.5 kHz
Max. counting rate attenuated	30 Hz
Minimum pulse length, drive unit	15 ms
Minimum pulse length, return	15 ms
Upper threshold value DC	5 ... 30 V
Power supply	Lithium battery
Lower threshold value DC	< 0.7 V
CE symbol (see declaration of conformity)	according to EU-EMV guideline
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 50 °C
Product weight	30 g
Setting clock pulse input	Negative edge 30 Hz
Clock pulse input (input)	Programmable
Mounting type	Front panel installation
Materials note	Conforms to RoHS
Material housing	PC