



Solenoid valve

CPE14-M1CH-3GL-1/8

Part number: 550247
Classic - do not use for new projects

FESTO

Very compact assembly, with M8 plug connection.
Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

| Feature | Value |
|---|--|
| Valve function | 3/2 closed, monostable |
| Type of actuation | electrical |
| Width | 14 mm |
| Standard nominal flow rate | 900 l/min |
| Operating pressure MPa | 0.25 ... 0.8 MPa |
| Working pressure | 2.5 ... 8 bar |
| Design structure | Piston slide |
| Type of reset | Air spring |
| Maritime classification | see certificate |
| Protection class | IP65 IP67 with plug socket to IEC 60529 |
| Nominal size | 6 mm |
| Sealing principle | soft |
| Assembly position | Any |
| Manual override | with accessories, detenting Pushing |
| Type of piloting | Piloted |
| Pilot air supply | Internal |
| Flow direction | non reversible |
| Valve position identification | Label holder |
| Lap | Positive overlap |
| Switching time off | 27 ms |
| Switching time on | 16 ms |
| Duty cycle | 100 % |
| Max. positive test pulse with logic 0 | 1,200 µs |
| Max. negative test pulse with logic 1 | 900 µs |
| Characteristic coil data | 24 V DC: 1.28 W |
| Permissible voltage fluctuation | -15 % / +10 % |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Vibration resistance | Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Medium temperature | -5 ... 50 °C |
| Ambient temperature | -5 ... 50 °C |
| Max. tightening torque plug | 0.4 Nm |

| Feature | Value |
|------------------------------|-------------------|
| Product weight | 60 g |
| Electrical connection | 4-pin M8x1 |
| Mounting type | with through hole |
| Pilot exhaust port 82 | M3 |
| Pilot air port 12 | M3 |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 2 | G1/8 |
| Pneumatic connection, port 3 | G1/8 |
| Materials note | Conforms to RoHS |
| Material seals | NBR |
| Material housing | Aluminum die cast |