


Compact cylinder ADNGF-63-60-P-A

Part number: 554275

FESTO

According to ISO 21287, with plain-bearing guide, piston rod secured against rotation by means of guide rods and yoke plate.



Data sheet

| Feature | Value |
|--|---|
| Stroke | 60 mm |
| Piston diameter | 63 mm |
| Based on the standard | ISO 21287 |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Design structure | Piston Piston rod Profile barrel |
| Position detection | For proximity sensor |
| Protection against torque/guide | Guide rod with yoke |
| Operating pressure MPa | 0.1 ... 1 MPa |
| Working pressure | 1 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 ... 80 °C |
| Impact energy in end positions | 1.3 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 1,750 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 1,870 N |
| Moving mass with 0 mm stroke | 373 g |
| Additional mass factor per 10 mm of stroke | 29 g |
| Basic weight for 0 mm stroke | 915 g |
| Additional weight per 10 mm stroke | 72 g |
| Pneumatic connection | G1/8 |
| Materials note | Conforms to RoHS |
| Material of flange screw | Steel |
| Material cover | Anodised wrought aluminium alloy |
| Material seals | TPE-U(PUR) |
| Material end plate | Anodised wrought aluminium alloy |
| Material piston rod | High alloy steel |
| Material cylinder barrel | Smooth-anodised wrought aluminium alloy |