

# Micro filter

## MS9-LFM-N3/4-AUM-HF-DA

Part number: 552988

FESTO

0.01 µm filter, metal bowl guard, high flow rate, manual condensate drain, with differential pressure indicator, flow direction from left to right.



### Data sheet

Feature	Value
Series	MS
Size	9
Design structure	Fiber filter
Grade of filtration	0.01 µm
Condensate drain	manual rotary
Working pressure	0 ... 20 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4]
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [1:7:2]
Max. standard flow rate for air quality class	7,800 l/min
Min. standard flow rate for air quality class	390 l/min
Filter efficiency	99.9999 %
Max. condensate volume	225 ml
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Storage temperature	-10 ... 60 °C
Residual oil content	0.01 mg/m <sup>3</sup>
Differential pressure display	Visual indicator
Mounting type	Line installation with accessories Optional
Assembly position	Vertical +/- 5°
Pneumatic connection, port 1	3/4 NPT
Pneumatic connection, port 2	3/4 NPT
Material housing	Aluminum die cast
Material of cover	PA
Material filter	Boron silicate fiber
Material bowl	Wrought Aluminum alloy
Material screen	PA
Material seals	NBR
Product weight	2,500 g