

Plastic tubing PUN-V0-10X2-BL-C

Part number: 561704

FESTO

Flame retardant



Data sheet

| Feature | Value |
|---|---|
| Outside diameter | 10 mm |
| Bending radius relevant for flow rate | 42 mm |
| Inside diameter | 6 mm |
| Min. bending radius | 12 mm |
| Tubing characteristics | Suitable for energy chains |
| Operating pressure for entire temperature range | -0.095 ... 0.9 MPa |
| Operating pressure complete temperature range | -0.95 ... 9 bar |
| Operating pressure for entire temperature range | -13.775 ... 130.5 psi |
| Temperature-dependent operating pressure | -0.095 ... 1.6 MPa |
| Temperature dependent working pressure | -0.95 ... 16 bar |
| Temperature-dependent operating pressure | -13.775 ... 232 psi |
| Note on working pressure | Water: max. 0.6 MPa at max. 50°C For applications with welding spatter: max. 1 MPa at 20°C, max. 0.9 MPa at 40°C, max. 0.7 MPa at 60°C |
| Authorization | TÜV |
| Certificate issuing department | B 013277 0506 00 |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] Water (liquid, free of ice) |
| Material fire test | UL94 V-0 (3mm) UL94 V-2 (0,75mm) |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | -35 ... 60 °C |
| Note on ambient temperature | For unpressurised use up to 90 °C |
| Product weight according to length | 0.064 kg/m |
| Pneumatic connection | For push-in connector outside diameter 10 mm for barbed connector internal diameter 6 mm |
| Color | blue |
| Note on color | Due to flame protection deviation from the standard color |
| Shore hardness | D 54 +/-3 |
| Materials note | Conforms to RoHS |
| Material tubing | TPE-U(PU) |