


Handling module HSW-10-AP-AW

Part number: 562559

FESTO

Pick and Place for repositioning parts at an angle of 90°, with additional rest position.



Data sheet

Feature	Value
Working stroke	9 ... 15 mm
Size	10
Max. linear stroke at 90° swivel angle	90/90 mm
Maximum Z-stroke, wait position	10 mm
Z stroke	80 ... 100 mm
Cushioning	CC: Shock absorber at both ends Soft characteristic
Assembly position	Any
Design structure	linear guide plus rotating bearing Swivel actuator guided motion sequence
Position detection	For proximity sensor
Working pressure	4 ... 8 bar
Minimum cycle time	0.6 s
Repetition accuracy, end positions	+/-0,02 mm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B2-L
Ambient temperature	0 ... 60 °C
Max. torque Mx	0.6 Nm
Max. torque My	0.6 Nm
Max. torque Mz	0.6 Nm
Maximum effective load	0.5 kg
Maximum process force in Y direction	30 N
Theoretical force at 0.6 MPa (6 bar, 87 psi)	30 N
Product weight	1,360 g
Mounting type	With through-hole and centering sleeve
Pneumatic connection, wait position	M5
Pneumatic connection	M3
Material stops	High alloy steel
Material spring pressure piece	High alloy steel
Material sub-base	Wrought Aluminum alloy Anodized
Material bracket	Wrought Aluminum alloy Anodized
Material cross-guide	Heat-treatment steel
Material swivel lever	Case-hardened steel Burnished
Material slotted guide plate	Case-hardened steel Hardened
Material sensor rail	Wrought Aluminum alloy Anodized
Material bar	Wrought Aluminum alloy Anodized
Material adjusting screw	High alloy steel