

# Swivel/linear unit

## DSL-20-40-270-P-A-S2-KF-B

Part number: 556624

FESTO

For proximity sensing. Rotary and linear movement can be actuated simultaneously or independently of one another. Rotary movement of 0° - 270° infinitely adjustable.



## Data sheet

Feature	Value
Rotation angle adjustment range	0 ... 270 deg
Stroke	40 mm
Piston diameter	20 mm
Swivel angle	0 ... 272 deg
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Fine adjustment	-6 deg
Mode of operation	double-acting
Design structure	Rotary vane
Position detection	For proximity sensor
Variants	Through piston rod
Protection against torque/guide	with ball-bearing guide
Working pressure	2.5 ... 8 bar
Max. impact speed	500 mm/s
Max. swivel frequency at 0.6 MPa (6 bar, 87 psi)	2 Hz
Swivel angle backlash	0.05 deg
Repetition accuracy	1 deg
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 60 °C
Dynamic load torque	0.35 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	120.5 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	158 N
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	2.5 Nm
Permissible mass moment of inertia	0.00007 kgm <sup>2</sup>
Product weight	1,140 g
Basic weight for 0 mm stroke	1,140 g
Additional weight per 10 mm stroke	52 g
Mounting type	Clamped in T-slot with external (male) thread Optional
Pneumatic connection	M5
Material cover	Wrought Aluminum alloy Anodized
Material seals	TPE-U(PU)
Material housing	Wrought Aluminum alloy Smooth anodized
Material piston rod	Heat-treatment steel