


# Coupling EAMD-19-15-9-8X10

Part number: 557999

FESTO

drive component, which transmits the rotary motion of a stepper or servo motor



## Data sheet

Feature	Value
Holder diameter 1	9 mm
Holder diameter 2	8 mm
Size	19
Nominal length	15 mm
Assembly position	Any
Max. speed	10,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	0.445 kgmm <sup>2</sup>
Transferable torque	2 Nm
Product weight	13.5 g
Materials note	Conforms to RoHS