

Solenoid coil

VACC-S13-18-A1-2U

Part number: 562891

FESTO

for armature system F19, connection pattern type A, according to EN 175 301, 110 V DC and AC.



Data sheet

Feature	Value
Type of actuation	electrical
Assembly position	Any
Switching position indicator	No
Duty cycle	100 %
Insulation class	H
Characteristic coil data	110 V DC: 1.8 W 110 V AC: 50/60 Hz, power: 1.8 VA
Permissible voltage fluctuation	-15 % / +10 %
CE symbol (see declaration of conformity)	according to EU low voltage guideline
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Corrosion resistance classification CRC	4 - Very high corrosion stress
PWIS conformity	VDMA24364 zone III
Protection class	IP65
Ambient temperature	-20 ... 60 °C
Product weight	210 g
Electrical connection	Plug pattern type A to EN 175301-803 Plug to EN 175301-803
Materials note	Conforms to RoHS
Material solenoid coil	PA UP