


Semi-rotary actuator DSM-63-270-P1-A-B

Part number: 566213

FESTO



Data sheet

Feature	Value
Size	63
Cushioning angle	6 deg
Rotation angle adjustment range	0 ... 240 deg
Swivel angle	0 ... 240 deg
Cushioning	P1: Flexible cushioning rings/plates with stop at both ends
Assembly position	Any
Fine adjustment	-6 deg
Mode of operation	double-acting
Design structure	Rotary vane
Position detection	For proximity sensor
Operating pressure MPa	0.15 ... 1 MPa
Working pressure	1.5 ... 10 bar
Max. swivel frequency at 0.6 MPa (6 bar, 87 psi)	1.6 Hz
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 ... 60 °C
Max. axial force	500 N
Max. radial force	500 N
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	40 Nm
Permissible mass moment of inertia	0.45 kgm ²
Product weight	5,090 g
Mounting type	with internal (female) thread
Pneumatic connection	G1/4
Materials note	Conforms to RoHS
Material of drive shaft	Steel Nickel plated
Material seals	TPE-U(PU)
Material housing	Wrought Aluminum alloy