


Solenoid valve

VSVA-B-T32H-AD-D2-1R5L

Part number: 566992

FESTO



Data sheet

| Feature | Value |
|--|---|
| Valve function | 2x3/2 open/closed, monostable |
| Type of actuation | electrical |
| Width | 52 mm |
| Standard nominal flow rate | 2,200 l/min |
| Operating pressure MPa | 0.3 ... 1 MPa |
| Working pressure | 3 ... 10 bar |
| Design structure | Piston slide |
| Type of reset | Air spring |
| Authorization | C-Tick c CSA us (OL) c UL us - Recognized (OL) |
| KC mark | KC-EMV |
| CE symbol (see declaration of conformity) | according to EU-EMV guideline |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC To UK RoHS instructions |
| Protection class | IP65 NEMA 4 |
| Nominal size | 15 mm |
| Grid dimension | 59 mm |
| Exhaust-air function | throttleable Via throttle plate Via individual sub-base |
| Sealing principle | soft |
| Assembly position | Any |
| Conforms to standard | ISO 5599-1 |
| Manual override | detenting Pushing |
| Type of piloting | Piloted |
| Pilot air supply | Internal |
| Flow direction | non reversible |
| Lap | Positive overlap |
| Signal status display | LED |
| Flow rate of valve | 3,000 l/min |
| Flow rate of valve on individual subbase | 2,000 l/min |
| Flow rate of pneumatically linked valve | 2,200 l/min |
| Switching time off | 35 ms |
| Switching time on | 20 ms |
| Duty cycle | 100 % |
| Max. positive test pulse with logic 0 | 1,000 µs |
| Max. negative test pulse with logic 1 | 3,500 µs |
| Nominal breakaway current per solenoid coil | 165 mA up to 30 ms |
| Nominal current with current reduction | 35 mA after 30 ms |
| Characteristic coil data | 24 V DC: 4.6 W |
| Permissible voltage fluctuation | +/- 10 % |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |

| Feature | Value |
|---|--|
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Vibration resistance | Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Medium temperature | -5 ... 50 °C |
| Relative air humidity | 0 - 90 % |
| Pilot medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 740 g |
| Electrical connection | 3-pin M12x1 Central plug Round design |
| Mounting type | On subbase |
| Pneumatic connection, port 1 | Connection plate size 2 as per ISO 5599-1 |
| Pneumatic connection, port 2 | Connection plate size 2 as per ISO 5599-1 |
| Pneumatic connection, port 3 | Connection plate size 2 as per ISO 5599-1 |
| Pneumatic connection, port 4 | Connection plate size 2 as per ISO 5599-1 |
| Pneumatic connection, port 5 | Connection plate size 2 as per ISO 5599-1 |
| Materials note | Conforms to RoHS |
| Material seals | FPM HNBR NBR |
| Material housing | Aluminum die cast PA |
| Material screws | Steel Galvanized |