



Solenoid valve

VUVS-L30-M32C-MD-G38-F8-1C1

Part number: 575570

★ Core product range

FESTO



Data sheet

| Feature | Value |
|---|--|
| Valve function | 3/2 closed, monostable |
| Type of actuation | electrical |
| Valve size | 31 mm |
| Standard nominal flow rate | 2,300 l/min |
| Operating pressure MPa | 0.25 ... 1 MPa |
| Working pressure | 2.5 ... 10 bar |
| Design structure | Piston slide |
| Type of reset | mechanical spring |
| Authorization | c UL us - Recognized (OL) |
| Protection class | IP65 with plug socket to IEC 60529 |
| Nominal size | 9.4 mm |
| Exhaust-air function | throttleable |
| Sealing principle | soft |
| Assembly position | Any |
| Manual override | detenting Pushing |
| Type of piloting | Piloted |
| Pilot air supply | Internal |
| Flow direction | non reversible |
| Lap | Positive overlap |
| b value | 0.3 |
| C value | 9.9 l/sbar |
| Switching time off | 58 ms |
| Switching time on | 16 ms |
| Duty cycle | 100 % |
| Max. positive test pulse with logic 0 | 2,000 µs |
| Max. negative test pulse with logic 1 | 3,600 µs |
| Characteristic coil data | 24 V DC: 3.3 W |
| Permissible voltage fluctuation | +/- 10 % |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Vibration resistance | Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Medium temperature | -10 ... 60 °C |
| Pilot medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 405 g |
| Electrical connection | Plug pattern type C to EN 175301-803 to EN 175301-803 |
| Mounting type | on manifold rail |

| Feature | Value |
|-------------------------------|-------------------------------|
| | with through hole Optional |
| Scavenging orifice connection | Non-ducted |
| Pilot exhaust port 82 | M5 |
| Pneumatic connection, port 1 | G3/8 |
| Pneumatic connection, port 2 | G3/8 |
| Pneumatic connection, port 3 | G3/8 |
| Materials note | Conforms to RoHS |
| Material seals | HNBR NBR |
| Material housing | Aluminum die cast Painted |
| Material Piston slide | Wrought Aluminum alloy |
| Material screws | Steel, nickel-plated |