


Linear gantry EXCT-15- -

Part number: 8026575

FESTO



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	15
Assembly position	Vertical
Design structure	Linear gantry
Working pressure	-0.95 ... 8 bar
Max. acceleration	50 m/s ²
Max. speed	4.8 m/s
Repetition accuracy	±0,1 mm
Duty cycle	100 %
PWIS conformity	VDMA24364 zone III
Storage temperature	-10 ... 60 °C
Relative air humidity	0 - 90 %
Sound pressure level	70 dB(A)
Protection class	IP40
Ambient temperature	10 ... 40 °C
Max. process force in Z direction	100 N
Rated load with maximum dynamic response	1.5 kg
Mounting type	With mounting kit With slot nuts
Materials note	Conforms to RoHS