


End plate VABE-S1-1RZ-G12

Part number: 8032668

FESTO



Data sheet

| Feature | Value |
|---|---|
| Width | 44 mm |
| Exhaust-air function | Via throttle plate |
| Based on the standard | ISO 5599-1 |
| Operating pressure MPa | 0 ... 1 MPa |
| Working pressure | 0 ... 10 bar |
| Suitability for vacuum | Yes |
| CE symbol (see declaration of conformity) | according to EU low voltage guideline |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 ... 60 °C |
| Medium temperature | -10 ... 50 °C |
| Pilot medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Ambient temperature | -10 ... 50 °C |
| Product weight | 410 g |
| Mounting type | Via through-hole for M6 screw |
| Auxiliary pilot air port 12/14 | G1/4 |
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 3 | G1/2 |
| Pneumatic connection, port 5 | G1/2 |
| Materials note | Conforms to RoHS |
| Material end plate | Aluminum die cast |