


Subbase

VABS-K1-7B-12-U14-P

Part number: 8047063

FESTO



Data sheet

Feature	Value
Nominal size	1.2 mm
Valve size	7 mm
Fluid connection	Female thread 1/4-28 UNF-2B
Assembly position	Any
Design structure	Connection direction underneath
Flow direction	reversible
Operating medium	Fluid media Gaseous media
Note on operating and pilot medium	Observe resistance of materials that come into contact with media
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 70 °C
Food-safe	See Supplementary material information
Medium temperature	0 ... 50 °C
Ambient temperature	0 ... 50 °C
Max. tightening torque, valve mounting	0.15 Nm
Max. tightening torque for fitting	0.6 Nm
Product weight	3 g
Mounting method for subbase	with through hole
Mounting method for valve	with internal (female) thread
Materials note	Conforms to RoHS
Material of connecting plate	PEEK
Material threaded sleeve	High alloy steel, non-corrosive