


# Code Reader SBSC-B-AF-R3B

Part number: 8058721  
Product to be discontinued

FESTO

Monochrome code reader with C-mount thread, Ethernet interface, RS 232 and PROFINET for reading barcodes and data matrix codes, expanded function.  
Type to be discontinued. Available until 2024. See Support Portal for alternative products.



## Data sheet

Feature	Value
Vision sensor version	Code reader
CE symbol (see declaration of conformity)	according to EU-EMV guideline
KC mark	KC-EMV
Authorization	RCM Mark c UL us - Listed (OL)
Field of vision	Dependent on the selected lens
Lens attachment	CS-Mount
Lighting type	Integrated
Sensor type	monochrome
Sensor resolution	736 x 480 pixels (WideVGA)
Image rate (frame)	50 fps
Max. number of test programs/jobs	255
Max. number of test criteria/detectors	255
Function of detectors/characteristics	EAN UPC RSS 2/5 Interleaved 2/5 Industrial Code 39 Code 93 Code 128 GS1 Pharmacode Codabar ECC200 QR-Code PDF 417
Typical cycle time	1D-Barcode: 30 ms 2D-Code: 40 ms
Information on Ethernet, connection technology	Socket M12 4-pin
Ethernet, data transmission speed	100 Mbit/s
Ethernet, supported protocols	Ethernet/IP FTP PROFINET SMB TCP/IP
Serial interface, connection technology	Plug M12 5-pin

Feature	Value
Serial interface, type	RS 232 / RS 422
Electrical connection	12-pin M12 Plug
Number of digital inputs	2
Number of digital outputs	2
Number of selectable digital inputs/outputs	4
Switching input	PNP/NPN, switchable
Switching level	Signal 0: $\leq 3$ V Signal 1: $\geq U_B - 1$ V
Switch output	PNP/NPN, switchable
Max. output current	50 mA
Short circuit strength	for all electrical connections
Nominal operating voltage DC	24 V
Permissible voltage fluctuation	-25 % / +10 %
Max. current consumption	550 mA
Current consumption with load-free outputs	200 mA
Ambient temperature	0 ... 50 °C
Storage temperature	-20 ... 60 °C
Protection class	IP65
Note on degree of protection	With protective tube
Dimensions W x L x H	45 mm x 45 mm x 76,7 mm
Product weight	160 g
Material housing	Anodised wrought aluminium alloy
Material cover	ABS-reinforced
Materials note	Conforms to RoHS
Vibration resistance	as per EN 60068-2-6
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27