


Subbase VMPA14-IC-AP-1-EX1E

Part number: 8023668

FESTO



Data sheet

Feature	Value
Width	24.4 mm
Length	107.3 mm
Grid dimension	14.9 mm
Operating pressure MPa	0.3 ... 0.8 MPa
Working pressure	3 ... 8 bar
Pilot pressure MPa	0.3 ... 0.8 MPa
Pilot pressure	3 ... 8 bar
Authorization	c UL us - Recognized (OL)
KC mark	KC-EMV
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU-Ex protection guideline (ATEX) in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK EX instructions To UK RoHS instructions
Explosion protection certification outside the EU	EPL Gc (GB)
ATEX category Gas	II 3G
Explosion ignition protection type Gas	Ex ec IIC T4 Gc X
Explosion-proof ambient temperature	-5 °C ≤ Ta ≤ +50 °C
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 ... 50 °C
Product weight	150 g
Electrical connection	M8 Plug
Mounting method for subbase	with through hole
Pneumatic connection, port 1	M7 G1/8
Pneumatic connection, port 2	M7 G1/8
Pneumatic connection, port 3	M7 G1/8
Pneumatic connection, port 4	M7 G1/8
Pneumatic connection, port 5	M7 G1/8
Materials note	Conforms to RoHS
Material of connecting plate	Aluminum die cast