



Holding brake DACs-25-A-S

Part number: 8072772

FESTO



Data sheet

Feature	Value
Assembly position	Any
Type of clamping with direction of action	at both ends Clamping with spring, release with compressed air
Position detection	For proximity sensor
Safety function	Holding and stopping a movement
Performance level (PL)	Stopping, holding, blocking a movement/category 1, Performance Level c
Operating pressure MPa	0.38 ... 0.8 MPa
Working pressure	3.8 ... 8 bar
Operating pressure	55.1 ... 116 psi
Max. permissible test pressure	8 bar
Minimum release pressure	3.8 bar
Round material to be clamped	25 mm
Authorization	TÜV
CE symbol (see declaration of conformity)	according to EU machines guideline
UKCA marking (see declaration of conformity)	To UK instructions for machines
Certificate issuing department	TÜV CA 697
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 80 °C
Static holding force	8,200 N
Product weight	12,832 g
Mounting type	with internal (female) thread with accessories
Release connection, clamping unit	G3/8
Materials note	Conforms to RoHS
Material seals	NBR TPE-U(PU)
Material spring	High alloy steel
Material housing	Steel
Material clamp jaws	Tool steel
Material piston	Steel