


Object Sensor SBSC-Q-AF-R3B

Part number: 8058728
Product to be discontinued

FESTO

Monochrome object sensor with C-mount thread, Ethernet interface, RS 232 and PROFINET for various tasks such as checking for presence and quality inspection, expanded function.

Type to be discontinued. Available until 2024. See Support Portal for alternative products.



Data sheet

Feature	Value
Vision sensor version	Object sensor
CE symbol (see declaration of conformity)	according to EU-EMV guideline
KC mark	KC-EMV
Authorization	RCM Mark c UL us - Listed (OL)
Field of vision	Dependent on the selected lens
Lens attachment	CS-Mount
Sensor type	monochrome
Sensor resolution	736 x 480 pixels (WideVGA)
Image rate (frame)	50 fps
Max. number of test programs/jobs	255
Max. number of test criteria/detectors	255
Function of detectors/characteristics	Position tracking via contour Pattern matching Contour matching Edge detection Contrast Brightness Grey value threshold Vernier caliper BLOB
Typical cycle time	Position tracking: 30 ms Pattern matching: 20 ms Contour matching: 30 ms Contrast: 4 ms Brightness: 2 ms Grey value threshold: 4 ms Vernier calliper: 8 ms BLOB: 30 ms
Information on Ethernet, connection technology	Socket M12 4-pin
Ethernet, data transmission speed	100 Mbit/s
Ethernet, supported protocols	Ethernet/IP FTP PROFINET SMB TCP/IP
Serial interface, connection technology	Plug M12

Feature	Value
	5-pin
Serial interface, type	RS 232 / RS 422
Electrical connection	12-pin M12 Plug
Number of digital inputs	2
Number of digital outputs	2
Number of selectable digital inputs/outputs	4
Switching input	PNP/NPN, switchable
Switching level	Signal 0: ≤ 3 V Signal 1: $\geq U_B - 1$ V
Switch output	PNP/NPN, switchable
Max. output current	50 mA
Short circuit strength	for all electrical connections
Nominal operating voltage DC	24 V
Permissible voltage fluctuation	-25 % / +10 %
Max. current consumption	550 mA
Current consumption with load-free outputs	200 mA
Ambient temperature	0 ... 50 °C
Storage temperature	-20 ... 60 °C
Protection class	IP67
Note on degree of protection	With protective tube
Dimensions W x L x H	45 mm x 45 mm x 76,7 mm
Product weight	160 g
Material housing	Anodised wrought aluminium alloy
Material cover	ABS-reinforced
Materials note	Conforms to RoHS
Vibration resistance	as per EN 60068-2-6
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27