


Angle seat valve

VZXA-A-TS6-65-M2-V13T-8-M-90-26-PR-V4

Part number: 8060519

FESTO

Modular, pneumatically actuated angle seat valve in stainless steel.
Over seat version, safety position closed, G-thread, nominal width DN65.



Data sheet

Feature	Value
Design structure	Poppet valve with diaphragm actuator
Type of actuation	pneumatic
Assembly position	Any
Mounting type	Line installation
Line connection	G2½ threaded collar to DIN ISO 228
Valve function	2/2
Flow direction	non reversible
Pressure of medium	0 ... 0.8 MPa
Medium pressure	0 ... 8 bar
Type of reset	mechanical spring
Type of piloting	With external control
Pneumatic connection	Female thread G1/8
Operating pressure MPa	0.5 ... 0.7 MPa
Working pressure	5 ... 7 bar
Operating pressure	72.5 ... 101.5 psi
Medium	Vapour Inert gases Filtered compressed air, degree of filtration 200 µm
Flow direction	Above valve seat, for gaseous media
Control of the medium	On/off operation
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Max. viscosity	600 mm ² /s
Medium temperature	-10 ... 180 °C
Ambient temperature	0 ... 60 °C
Flow rate Kv	77.4 m ³ /h
Outdoor use	C1 - weather protected locations of use
Materials note	Conforms to RoHS
PWIS conformity	VDMA24364 zone III
Material process valve housing	Stainless steel casting
Material number, process valve housing	1.4409
Material seals	NBR
Material spindle seal	PTFE
Material seat seal	PTFE
Product weight	10,185 g
Authorization	CRN
CE symbol (see declaration of conformity)	according to EU printing device guideline
UKCA marking (see declaration of conformity)	UK regulation for pressure equipment
Certificate issuing department	TÜV 968/V 1039.01/20
Safety Integrity Level (SIL)	SIL 2
Probability of Failure per Hour in [1/h].	1.36E-07
PFD (Probability of Failure on Demand)	5.95E-04
Actuator size	90 mm
Stroke	26 mm

Feature	Value
Control function	Closed via reduced spring force, NC
Position detection	With mechanical indicator
Material drive housing	Stainless steel casting
Material number, actuator housing	1.4408
Storage temperature	-10 ... 60 °C
Protection class	IP65 IP67
Material piston rod	High alloy steel, non-corrosive
Material cover	Stainless steel casting