

Compact cylinder

ADN-32-40-A-PPS-A-C

Part number: 8076065

FESTO

Type to be discontinued. Available until 2022. See Support Portal for alternative products.



Data sheet

Feature	Value
Stroke	40 mm
Piston diameter	32 mm
Piston rod thread	M10x1,25
Cushioning	PPS: Self-adjusting pneumatic end-position cushioning
Assembly position	Any
Conforms to standard	ISO 21287
Piston-rod end	Male thread
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	Single-ended piston rod
Operating pressure MPa	0.15 ... 1 MPa
Working pressure	1.5 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 80 °C
Impact energy in end positions	1 J
Cushioning length	4 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	415 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	483 N
Moving mass with 0 mm stroke	53 g
Additional weight per 10 mm stroke	36 g
Basic weight for 0 mm stroke	223.5 g
Additional mass factor per 10 mm of stroke	9 g
Mounting type	with through hole with internal (female) thread with accessories Optional
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover	Wrought Aluminum alloy
Material seals	TPE-U(PUR)
Material piston rod	High alloy steel
Material cylinder barrel	Wrought Aluminum alloy Smooth anodized