


Compact cylinder

AEN-S-12-10-I-P

Part number: 8076476

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 10 mm |
| Piston diameter | 12 mm |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Mode of operation | pushing action |
| Piston-rod end | Female thread |
| Design structure | Piston Piston rod |
| Variants | Single-ended piston rod |
| Operating pressure MPa | 0.1 ... 1 MPa |
| Working pressure | 1 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Ambient temperature | 0 ... 60 °C |
| Impact energy in end positions | 0.022 J |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 8 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 60 N |
| Moving mass with 0 mm stroke | 3.5 g |
| Additional mass factor per 10 mm of stroke | 2 g |
| Basic weight for 0 mm stroke | 26 g |
| Additional weight per 10 mm stroke | 15 g |
| Mounting type | with through hole with internal (female) thread with accessories Optional |
| Pneumatic connection | M5 |
| Materials note | Conforms to RoHS |
| Material cover | Anodised wrought aluminium alloy |
| Material of dynamic seals | NBR |
| Material housing | Anodised wrought aluminium alloy |
| Material piston rod | High alloy steel, non-corrosive |