


Connecting cable NEBA-M8W4-U-5-N-LE4

Part number: 8078234

FESTO



Data sheet

Feature	Value
Conforms to standard	EN 61076-2-104 EN 61984
Certification	c UL us - Listed (OL)
Intended use	The connecting cable connects field devices (sensors, actuators) with controllers.
Certificate issuing authority	UL E253748
Cable designation	Without label holder
Contact durability	100
Product weight	129 g
Application note	Meets the requirements of IEC 61010-1 and 61010-2-202, in particular for electrically operated valves from Festo. Only energy-limited circuits with a maximum current of 4 A at a max. open circuit voltage of 30 VDC are permitted to be used for supplying electrically actuated valves from Festo.
Electrical connection 1, function	Field device end
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw-type lock with hexagon AF 9 and longitudinal knurl rotatable Compatible with rotatable/non-rotatable screw lock
Electrical connection 1, terminal allocation	Pin 1 = BN Pin 2 = WH Pin 3 = BU Pin 4 = BK
Electrical connection 1, display	without
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	4

Feature	Value
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, terminal allocation	Pin 1 = BN Pin 2 = WH Pin 3 = BU Pin 4 = BK
Electrical connection 2, display	without
DC operating voltage range	0 V...60 V
Note on operating voltage range DC	0 - 30 V for UL applications NEC/CEC CLASS 2
Operating voltage range AC	0 V...48 V
Note on operating voltage range AC	0 - 30 V for UL applications NEC/CEC CLASS 2
Current rating at 40° C	4 A
Surge resistance	1.5 kV
Cable length	5 m
Cable characteristic	Suitable for energy chains/robot applications abrasion-resistant low adhesion Flame-retardant and self-extinguishing
Connector cable test conditions	Test conditions on request Torsion resistance: > 300,000 cycles, ±270°/0.1 m Flexural strength: > 50000 cycles, bending radius 5 mm Energy chain > 5 million cycles, bending radius 28 mm
Note on connector cable test conditions	tested at 23 °C
Bending radius, fixed cable installation	14 mm
Bending radius, flexible cable installation	46 mm
Cable diameter	4.5 mm
Cable design	4 x 0.25 mm ²
Nominal conductor cross section	0.25 mm ²
Wire ends	Stripped Cut off bluntly
Degree of protection	IP65 IP68 IP69K
Special features	UV-resistant hydrolysis resistant Resistant to cooling lubricants Resistant to microbes Oil-resistant Ozone-resistant
Use in exterior area	Locations of use with direct outdoor climatic exposure Class D1 based on IEC 60654-1
Ambient temperature	-40 °C...85 °C
Note on ambient temperature	-40 - 50 °C for UL applications
Ambient temperature with flexible cable installation	-20 °C...85 °C
Note on ambient temperature with flexible cable installation	-20 - 50 °C for UL applications
Storage temperature	-25 °C...55 °C
Note on storage temperature	short-term for transport in packaging -40 ... 85 °C
Relative air humidity	Max. 93% at 40 °C
Nominal altitude of use above sea level	<= 2000 m NHN
Overvoltage category	II
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 4 according to ISO 14644-1

Feature	Value
Note on materials	CFC-free RoHS-compliant Cadmium-free Halogen-free Free of phosphoric acid ester
Contamination level	3
Corrosion resistance class (CRC)	1 - Low corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray
Housing material	TPE-U(PUR)
Housing colour	Black
Material of screw-type lock	Die-cast zinc, nickel-plated
Seals material	FPM
Material of pin contacts	Copper alloy, gold-plated
Insulating sheath material	PP