


# digital input/output module

## CPX-AP-I-4DI4DO-M8-3P

Part number: 8086601

★ Core product range

FESTO



## Data sheet

Feature	Value
Dimensions W x L x H	30 mm x 170 mm x 35 mm
Mounting type	On H-rail with accessories with through hole
Product weight	129 g
Ambient temperature	-20 ... 50 °C
Storage temperature	-40 ... 70 °C
Relative air humidity	5 - 95 % non-condensing
Protection class	IP65 IP67
Note on degree of protection	Unused connections sealed
Corrosion resistance classification CRC	1 - Low corrosion stress
Max. line length	30 m outputs 30 m inputs 50 m system communication
Note on max. cable length	Power supply according to nominal voltage
PWIS conformity	VDMA24364-B2-L
CE symbol (see declaration of conformity)	according to EU-EMV guideline
UKCA marking (see declaration of conformity)	To UK instructions for EMC
KC mark	KC-EMV
Authorization	RCM Mark c UL us - Listed (OL)
Certificate issuing department	UL E239998
Materials note	Conforms to RoHS
Material housing	PA PC Nickel-plated die-cast zinc
Material o-ring	FPM
Diagnostics via LED	Diagnostics per module Power supply load Status per channel
Diagnostics per internal communication	Load switch-off Short-circuit/overload output signal Short circuit/overload in sensor supply Electronics/sensors overvoltage Load overvoltage Electronics/sensors undervoltage Load undervoltage
No. of outputs	4
Communication interface, function	System communication XF10 IN / XF20 OUT
Communication interface, connection type	2x socket
Communication interface, connection technology	M8x1, D-coded in accordance with EN 61076-2-114
Communication interface, number of pins/wires	4
Communication interface, protocol	AP
Communication interface, screening	Yes
Power supply, function	Incoming electronics/sensors and load

<b>Feature</b>	<b>Value</b>
Power supply, type of connection	Plug
Power supply, connection technology	M8x1, A-coded to EN 61076-2-104
Power supply, number of pins/wires	4
Power transmission, function	Outgoing electronics/sensors and load
Power transmission, connection type	Plug socket
Power transmission, connection technology	M8x1, A-coded to EN 61076-2-104
Power transmission, number of pins/wires	4
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Nominal operating voltage, DC outputs	24 V
Permissible voltage fluctuations, load	± 25 %
Nominal operating voltage DC for electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25 %
Max. power supply	2 x 4 A (external fuse required)
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Type 35 mA
Intrinsic current consumption at nominal operating voltage load	Typical 10 mA
Power failure buffering	10 ms
Polarity protected	Yes
Electrical connection, input, function	Digitaleingang
Electrical connection, input, connection type	4x socket
Electrical connection, input, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection, input, number of pins/wires	3
No. of inputs	4
Input characteristics	to IEC 61131-2, type 3
Switching level	Signal 0: ≤ 5 V Signal 1: ≥ 11 V
Input circuit logic	PNP (positive-switching) 2-wire sensors to IEC 61131-2 3-wire sensors to IEC 61131-2
Input debounce time	0,1 ms 3 ms 10 ms 20 ms
Fuse protection of inputs (short circuit)	Internal electronic fuse protection per module
Max. residual current inputs per module	1.8 A
Electrical isolation of inputs between channels	No
Electrical isolation of inputs between channel - internal communication	Yes
Electrical connection, output, function	Digitalausgang
Electrical connection, output, connection type	4x socket
Electrical connection, output, connection technology	M8x1, A-coded to EN 61076-2-104
Electrical connection, output, number of pins/wires	3
Characteristic curve, outputs	to IEC 61131-2, type 0.5
Switching logic, outputs	PNP (positive-switching)
Fuse protection of outputs (short circuit)	Internal electronic fuse protection per channel
Output delay with resistive load	Signal change 0→1: < 200 µs Signal change 1→0: < 200 µs
Max. residual current outputs per module	2 A
Electrical isolation of outputs between channels	No
Electrical isolation of outputs between channel - internal communication	Yes
Max. power supply per channel	0,5 A