


Parallel gripper DHPC-6-A-NO-S

Part number: 8116741

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | 6 |
| Stroke per gripper jaw | 2 mm |
| Max. replacement accuracy | 0.2 mm |
| Max. angular gripper jaw backlash ax,ay | 0 deg |
| Max. gripper jaw backlash Sz | 0 mm |
| Rotationally symmetrical | ≤ 0.2 mm |
| Repetition accuracy, gripper | ≤ 0.02 mm |
| Number of gripper fingers | 2 |
| Drive system | pneumatic |
| Assembly position | Any |
| Mode of operation | single-acting open |
| Gripper function | Parallel |
| Gripper force back-up | On opening |
| Design structure | Connection direction at side Lever Standard mounting of gripper fingers guided motion sequence |
| Guide | Ball guide |
| Position detection | For proximity sensor |
| Variants | Recommended for production facilities for the manufacture of lithium-ion batteries |
| Total gripping force at 0.6 MPa (6 bar, 87 psi), closing | 7.8 N |
| Operating pressure MPa | 0.35 ... 0.8 MPa |
| Working pressure | 3.5 ... 8 bar |
| Operating pressure | 50.75 ... 116 psi |
| Max. operating frequency of gripper | 3 Hz |
| Min. opening time at 0.6 MPa (6 bar, 87 psi) | 16 ms |
| Min. closing time at 0.6 MPa (6 bar, 87 psi) | 16 ms |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| RSBP classification to CD-0033 | F1a |
| Ambient temperature | -10 ... 60 °C |
| Gripping force per gripper jaw at 0.6 MPa (6 bar, 87 psi) closing | 3.9 N |
| Mass moment of inertia | 0.012 kgcm ² |
| Max. force on gripper jaw Fz static | 5 N |
| Max. torque at gripper Mx static | 0.02 Nm |
| Max. torque at gripper My static | 0.04 Nm |
| Max. torque at gripper Mz static | 0.02 Nm |
| Product weight | 27 g |
| Mounting type | Direct mounting via through-holes Direct mounting via threads Optional |
| Pneumatic connection | M3 |
| Materials note | Conforms to RoHS |
| Material housing | Anodised aluminium |
| Material gripper jaws | High alloy steel, non-corrosive |