

Control System CMCB-D1-CC-S0

Part number: 8118456

FESTO



Data sheet

Feature	Value
Instructions for use	The product is suitable for industrial purposes only. Measures for interference suppression may be required in residential areas.
Design structure	Control cabinet
Performance level (PL)	Category B, Performance Level b
Dimensions W x L x H	220 mm x 350 mm x 440 mm
Protection (short circuit)	Internal electronic fuse
Max. current consumption	1.1 A
Current consumption of the secondary circuit	5 A
Max. power supply	6 A
Nominal operating voltage, AC	230 V
Mains types	TT TN IT
Line frequency	50 ... 60 Hz
Degree of contamination	2
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU low voltage guideline
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	Max. 50% at 40 °C
Protection against direct and indirect contact	Safety extra-low voltage with safe disconnection (PELV) Earthing of all exposed conductive parts
Protection class	IP54
Ambient Conditions	Interior
Ambient temperature	5 ... 40 °C
Nominal altitude of use	1000 m NN
Product weight	15 kg
Electrical connection	Cage clamp terminal Push-in
Materials note	Conforms to RoHS