


Filter regulator PCRP-44-G12-12-E-R1-M-T18

Part number: 8120904

FESTO



Data sheet

Feature	Value
Size	44
Series	P
Actuator lock	Adjusting screw with lock
Assembly position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	manual rotary
Design structure	Filter regulator without pressure gauge
Conforms to standard	NACE MR0175/ISO 15156 (housing and bowl)
Max. condensate volume	12 cm ³
Controller function	with initial pressure compensation with secondary exhaust
Pressure gauge	Prepared for G1/4
Operating pressure MPa	0.1 ... 2 MPa
Working pressure	1 ... 20 bar
Pressure regulation range	0.5 ... 12 bar
Max. pressure hysteresis	0.2 bar
Max. standard flow rate	2,500 l/min
Standard nominal flow rate	1,750 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [-:4:-] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 80 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Medium temperature	-20 ... 80 °C
Ambient temperature	-20 ... 80 °C
Product weight	755 g
Mounting type	Line installation With mounting kit Optional
Pressure gauge connection	G1/4
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 2	G1/2
Material of drain screw	High alloy steel, non-corrosive
Material number of drain screw	1.4404/316L
Material of filter holder	POM
Materials note	Conforms to RoHS
Material mounting bracket	High alloy steel, non-corrosive
Material seals	CR NBR
Material spring	High alloy steel, non-corrosive
Material filter	PE
Material housing	Stainless steel casting
Material number for housing	1.4409/CF3M(316L)
Material adjusting screw	High alloy steel, non-corrosive
Material bowl	Stainless steel casting
Material number of bowl	1.4409/CF3M (316L)