



Mini slide

EGSC-BS-KF-32-50-3P

Part number: 8162074

FESTO



Data sheet

Feature	Value
Working stroke	50 mm
Size	32
Stroke reserve	0 mm
Reversing backlash	150 µm
Spindle diameter	8 mm
Spindle pitch	3 mm/U
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	Electric mini slide With ball screw
Motor type	Stepper motor Servomotor
Referencing	Fixed stop block positive Fixed stop block negative Reference switch
Spindle type	Ball screw
Position detection	For proximity sensor
Max. acceleration	5 m/s ²
Max. speed	0.188 m/s
Repetition accuracy	±0,015 mm
Duty cycle	100 %
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364 zone III
RSBP classification to CD-0033	F1a
Cleanroom class	ISO class 9
Sound pressure level	55 dB(A)
Protection class	IP40
Ambient temperature	0 ... 50 °C
Fixed bearing dynamic basic load rating	3,795 N
Linear guide dynamic basic load rating	2,135 N
Ball screw drive dynamic basic load rating	1,900 N
Max. force F _y	991 N
Max. force F _z	991 N
Max. torque M _x	3.4 Nm
Max. torque M _y	3.2 Nm
Max. torque M _z	3.2 Nm
Max. radial force at drive shaft	75 N
Max. feed force F _x	60 N
Reference value for working load, horizontal	6 kg
Reference value for working load, vertical	6 kg
Ball screw drive statistical basic load rating	3,300 N
Linear guide statistical basic load rating	3,880 N
Mass moment of inertia J _H per meter of stroke	0.02488 kgcm ²
Mass moment of inertia J _L per kg of working load	0.00228 kgcm ²
Mass moment of inertia, J _O	0.00394 kgcm ²
Feed constant	3 mm/U

Feature	Value
Fixed bearing statistical basic load rating	1,792 N
Reference value, running performance	5,000 km
Maintenance interval	Life-time lubrication
Moving mass with 0 mm stroke	149 g
Additional mass factor per 10 mm of stroke	12 g
Product weight	481 g
Basic weight for 0 mm stroke	331 g
Additional weight per 10 mm stroke	30 g
Mounting type	with internal (female) thread with centering sleeve with accessories With cylindrical dowel pin
Interface code, actuator	V25
Materials note	Conforms to RoHS
Material guide slide	Roller bearing steel
Material guide rail	Roller bearing steel
Material housing	Anodised wrought aluminium alloy
Material yoke plate	Wrought Aluminum alloy
Material piston rod	High alloy steel, non-corrosive
Material slide	Anodised wrought aluminium alloy
Material spindle nut	Roller bearing steel
Material spindle	Roller bearing steel