


Sub-base kit DADP-SP-G9-10-R

Part number: 8173533

FESTO



Data sheet

Feature	Value
Size	10
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Max. stop force	100 N
Max. tightening torque	0.8 Nm
Tightening torque tolerance	± 15 %
Product weight	52 g
Type of mounting	Direct fastening via thread
Note on materials	RoHS-compliant
Stops material	High-alloy steel
Seals material	NBR
Plate material	Wrought aluminum alloy, anodized
Material of screws	Steel