



# Connecting cable NEBC-D8G4-ES-25-N-S-D8G4-ET-G2

Part number: 8176601

**FESTO**



## Data sheet

| Feature  | Value                                   |
|--|---|
| Based on norm                                  | EN 61076-2-114                          |
| Cable designation                              | Without label holder                    |
| Contact durability                             | 100                                     |
| Product weight                                 | 1462 g                                  |
| Electrical connection 1, function              | Control side                            |
| Electrical connection 1, design                | Round                                   |
| Electrical connection 1, connection type       | Plug                                    |
| Electrical connection 1, cable outlet          | Straight                                |
| Electrical connection 1, connection technology | M8x1, D-coded as per EN 61076-2-114     |
| Electrical connection 1, number of pins/wires  | 4                                       |
| Electrical connection 1, occupied pins/wires   | 4                                       |
| Electrical connection 1, type of mounting      | Screw-type lock with longitudinal knurl |
| Electrical connection 2, function              | Control side                            |
| Electrical connection 2, design                | Round                                   |
| Electrical connection 2, connection type       | Plug                                    |
| Electrical connection 2, cable outlet          | Straight                                |
| Electrical connection 2, connection technology | M8x1, D-coded as per EN 61076-2-114     |
| Electrical connection 2, number of pins/wires  | 4                                       |
| Electrical connection 2, occupied pins/wires   | 4                                       |
| Electrical connection 2, type of mounting      | Screw-type lock with longitudinal knurl |
| DC operating voltage range                     | 0 V...30 V                              |
| Nominal operating voltage DC                   | 24 V                                    |
| Current rating at 40° C                        | 3 A                                     |
| Surge resistance                               | 1.5 kV                                  |
| Reverse polarity protection                    | no                                      |
| Protective earth connection                    | Not available                           |
| Shield   | yes                                     |
| Transmission characteristics                   | as per system communication AP          |
| Cable length                                   | 25 m                                    |
| Cable characteristic                           | Suitable for energy chains              |

| Feature  | Value                            |
|--|----------------------------------|
| Connector cable test conditions                      | Test conditions on request       |
| Bending radius, fixed cable installation             | 20 mm                            |
| Bending radius, flexible cable installation          | 75 mm                            |
| Cable diameter                                       | 6.3 mm                           |
| Cable diameter tolerance                             | ± 0.2 mm                         |
| Cable design   | 1 x (4 x AWG22)                  |
| Nominal conductor cross section                      | AWG22                            |
| Degree of protection                                 | IP65<br>IP67                     |
| Note on degree of protection                         | In mounted state                 |
| Special features                                     | Oil-resistant                    |
| Ambient temperature                                  | -20 °C...60 °C                   |
| Ambient temperature with flexible cable installation | -5 °C...60 °C                    |
| Storage temperature                                  | -40 °C...70 °C                   |
| CE marking (see declaration of conformity)           | As per EU RoHS directive         |
| UKCA marking (see declaration of conformity)         | To UK RoHS instructions          |
| LABS (PWIS) conformity                               | VDMA24364-B2-L                   |
| Note on materials                                    | RoHS-compliant<br>Halogen-free   |
| Contamination level                                  | 3                                |
| Corrosion resistance class (CRC)                     | 2 - Moderate corrosion stress    |
| Material of cable sheath                             | TPE-U(PUR)                       |
| Color cable sheath                                   | Silver-grey with sky blue stripe |
| Housing material                                     | PA<br>TPE-U(PUR)                 |
| Housing colour                                       | Black                            |
| Material of screw-type lock                          | Brass, nickel-plated             |
| Seals material                                       | NBR                              |
| Material of pin contacts                             | Copper alloy, gold-plated        |
| Insulating sheath material                           | PP                               |