

**Piezo valve**  
**VEVP-XA-4-B-T32C-F-D22-2**  
 Part number: 8184037

**FESTO**



**Data sheet**

Feature	Value
Width dimension	16 mm
Valve function	3-way proportional pressure control valve closed
Structural design	Sub base valve
Sealing principle	Soft
Actuation type	Electrical
Suitability for vacuum	yes
Flow direction	Non-reversible
Standard flow rate	18 l/min
Degree of protection	IP65
LABS (PWIS) conformity	VDMA24364 zone III
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 3 according to ISO 14644-1
Note on materials	RoHS-compliant
Housing material	PA66-GF30 TPE-U(PU)
Seals material	NBR
Product weight	85.5 g
Nominal width	4 mm
Operating pressure	0.2 MPa 2 bar 29 psi
Nominal operating voltage DC	24 V
Storage temperature	-20 °C...70 °C
Temperature of medium	5 °C...50 °C
Ambient temperature	5 °C...50 °C
Relative air humidity	5 - 85 % Non-condensing
Climatic category	3K22 as per EN 60721
Pneumatic connection 2	Flange
Pneumatic connection 4	Flange

Feature	Value
Pneumatic connection 1	Flange
Pneumatic connection 3	Flange
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27