


Sub-base
VABS-K2-12S-20-G18-P
Part number: 8186871

FESTO



Data sheet

Feature	Value
Size	12
Nominal width	2 mm
Valve size	12 mm
Fluid connector	Internal thread G1/8
Mounting position	Any
Structural design	Connection direction at side
Max. no. of valve positions	1
Flow direction	Non-reversible
Operating medium	Liquid media Gaseous media
Information on operating and pilot media	Observe resistance of materials that come into contact with media
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...70 °C
For use in the food industry	See supplementary material information
Temperature of medium	0 °C...50 °C
Ambient temperature	0 °C...50 °C
Max. tightening torque for valve mounting	0.33 Nm
Max. tightening torque of pneumatic fitting	7 Nm
Max. tightening torque	0.6 Nm
Product weight	31 g
Sub-base mounting type	With through-hole
Pneumatic valve mounting type	With internal thread
Note on materials	RoHS-compliant
Material of sub-base	PEEK