

Push-on flange DARF-Q13-16-1

Part number: 8163622

FESTO



Data sheet

Feature	Value
Size	16
Mounting position	Any
Structural design	Adapter for rotary actuator
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 9 according to ISO 14644-1
Ambient temperature	0 °C...60 °C
Max. bending moment	4 Nm
Max. axial load static	140 N
Product weight	52 g
Type of mounting	Via through-hole and centering sleeve
Note on materials	RoHS-compliant
Material of flange	Wrought aluminum alloy, anodized
Sleeve material	High-alloy stainless steel
Material of screws	Steel, coated