

Servo Motor EMMT-...-40-

Part number: 8171399

FESTO



Data sheet

Feature	Value
Ambient temperature	-40 °C...40 °C
Note on ambient temperature	Up to 80 °C with derating of -2.25% per degree Celsius
Max. installation height	4000 m
Information on max. installation height	with 1,000 m and longer only with derating of -1.0% per 100 m
Storage temperature	-40 °C...70 °C
Relative air humidity	0 - 90 %
Conforms to standard	IEC 60034
Thermal class according to EN 60034-1	F
Max. winding temperature	155 °C
Rating class according to EN 60034-1	S1
Temperature monitoring	Digital motor temperature transmission via EnDat® 2.2 Dig. motor temp. via BiSS-C
Motor type as per EN 60034-7	IM B5 IM V1 IM V3
Mounting position	Any
Degree of protection	IP40 IP65
Note on degree of protection	IP40 for motor shaft without rotary shaft seal IP65 for motor shaft with rotary shaft seal
Concentricity, coaxiality, axial runout according to DIN SPEC 42955	N
Balancing quality	G 2.5
Detent torque	<1.0% of peak torque
Bearing lifetime, under nominal conditions	20000 h
Featherkey shaft design	DIN 6885 A 3 x 3 x 12
Interface code, motor out	40P
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connection technology	M17x0.75 M23x1
Electrical connection 1, number of pins/wires	12
Contamination level	2
Note on materials	RoHS-compliant

Feature	Value
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Certification	RCM compliance mark German Technical Control Board (TÜV) c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK instructions for electrical equipment
Certificate issuing authority	TÜV 968/INS 464.00/24 UL E342973
Nominal operating voltage DC	48 V...325 V
Type of winding switch	Star inside
Number of pole pairs	5
Stall torque	0.24 Nm...0.75 Nm
Nominal torque	0.21 Nm...0.69 Nm
Peak torque	0.83 Nm...2 Nm
Nominal rotary speed	3000 rpm...7000 rpm
Max. rotational speed	5760 rpm...15600 rpm
Angular acceleration	100000 rad/s ²
Motor nominal power	96 W...234 W
Continuous stall current	1.3 A...8.6 A
Motor nominal current	1 A...8.1 A
Peak current	5.4 A...20 A
Motor constants	0.055 Nm/A...0.33 Nm/A
Standstill torque constant	0.06 Nm/A...0.42 Nm/A
Voltage constant, phase-to-phase	3.6 mV/min...25.4 mV/min
Phase-phase winding resistance	0.41 Ohm...13.1 Ohm
Winding inductance phase-phase	0.57 mH...13.9 mH
Winding longitudinal inductivity Ld (phase)	0.22 mH...5.3 mH
Cross inductivity Lq (phase)	0.29 mH...6.9 mH
Electric time constant	0.82 ms...1.39 ms
Thermal time constant	4.6 min...21.4 min
Thermal resistance	1.05 K/W...1.58 K/W
Measuring flange	200 x 200 x 15 mm, steel
Total output inertia moment	0.039 kgcm ² ...0.138 kgcm ²
Product weight	500 g...1200 g
Permissible axial shaft load	30 N
Permissible radial shaft load	150 N
Rotor position sensor	Absolute encoder, single-turn Absolute encoder, multi-turn
Rotor position sensor for manufacturer designation	ECI 1119 EQI 1131 Festo iC-MHM KCD-BC33B-1617-JP4F-GRQ-009
Rotor position encoder for absolutely detectable revolutions	1 ...4096
Rotor position sensor interface	BiSS-C EnDat® 22
Rotor position sensor measuring principle	Magnetic Inductive
Rotor position encoder for DC operating voltage	5 V
Rotor position encoder for DC operating voltage range	3.6 V...14 V

Feature	Value
Rotor position encoder for positional values per revolution	65536 ...524288
Rotor position sensor resolution	16 bit...19 bit
Brake holding torque	0.45 Nm
Brake DC operating voltage	24 V
Brake power consumption	8.2 W
	1
Brake mass moment of inertia	0.0058 kgcm ²
Switching cycles, holding brake	10 million idle actuations (without friction work!)
MTTF, subcomponent	190 years, rotor position sensor