

# Digital output module CPX-AP-I-8DO-M12-5P

Part number: 8179439

FESTO



## Data sheet

Feature	Value
Dimensions W x L x H	30 mm x 170 mm x 35 mm
Type of mounting	On H-rail with accessories With through-hole
Product weight	127 g
Ambient temperature	-20 °C...50 °C
Storage temperature	-40 °C...70 °C
Relative air humidity	5 - 95 % Non-condensing
Degree of protection	IP65 IP67
Note on degree of protection	Unused connections sealed
Corrosion resistance class (CRC)	1 - Low corrosion stress
Max. cable length	30 m outputs 50 m system communication
Information on max. cable length	Power supply according to nominal voltage
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
CE marking (see declaration of conformity)	As per EU EMC directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
KC characters	KC EMC
Certification	RCM compliance mark c UL us - Listed (OL)
Certificate issuing authority	UL E239998
Note on materials	RoHS-compliant
Housing material	PA PC Die-cast zinc, nickel-plated
O-ring material	FPM
Diagnostics via LED	Diagnostics per module Load power supply Status per channel

Feature	Value
Diagnose per internal communication	Load switch-off Short-circuit/overload in output signal Electronics/sensors overvoltage Load overvoltage Electronics/sensors undervoltage Load undervoltage
No. of outputs	8
Communication interface, function	System communication XF10 IN / XF20 OUT
Communication interface, connection type	2x socket
Communication interface, connection technology	M8x1, D-coded as per EN 61076-2-114
Communication interface, number of pins/wires	4
Communication interface, protocol	AP
Communication interface, shielding	yes
Power supply, function	Incoming electronics/sensors and load
Power supply, type of connection	Plug
Power supply, connection technology	M8x1, A-coded as per EN 61076-2-104
Power supply, number of pins/wires	4
Voltage forwarding, function	Outgoing electronics/sensors and load
Voltage forwarding, connection type	Socket
Voltage forwarding, connection technology	M8x1, A-coded as per EN 61076-2-104
Voltage forwarding, number of pins/wires	4
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Nominal operating voltage DC load	24 V
Permissible voltage fluctuations load	± 25 %
Nominal operating voltage DC for electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25 %
Max. power supply	2 x 4 A (external fuse required)
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 35 mA
Intrinsic current consumption at nominal operating voltage load	Typically 10 mA
Power failure buffering	10 ms
Reverse polarity protection	yes
Electrical connection output, function	Digital output
Electrical connection output, connection type	4x socket
Electrical connection output, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical output connection, number of pins/wires	5
Characteristic curve outputs	As per IEC 61131-2, type 0.5
Switching logic at outputs	PNP (positive switching)
Fuse protection outputs (short circuit)	Internal electronic fuse per channel
Output delay with resistive load	Signal change 0->1: < 200 µs Signal change 1->0: < 200 µs
Max. residual current of outputs per module	2 A
Electrical isolation of outputs between channels	no
Electrical isolation of outputs between channel - internal communication	yes
Max. power supply per channel	0.5 A