

Axial kit
EAMM-A-N48-60G-G2
Part number: 8197469

FESTO



Data sheet

Feature	Value
Nominal length	46 mm
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	39 kgmm ²
Transferable torque	21 Nm
Product weight	454 g
Interface code, actuator	N48
Interface code, motor in	60G
Note on materials	RoHS-compliant