

Manifold subbase VABX-A-P-EL-E12-MF1-SHUH

Part number: 8188451
New

FESTO

Data sheet

Feature	Value
Max. number of solenoid coils	24
Dimensions W x L x H	45 mm x 104,3 mm x 53,3 mm
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Authorization	RCM Mark
KC mark	KC-EMV
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-20 ... 70 °C
Relative air humidity	5 - 95 %
Protection class	IP40
Ambient temperature	-5 ... 50 °C
Max. tightening torque, wall mounting	6 Nm
Product weight	124.1 g
Electrical connection 1, connection technology	Sub-D
Cable outlet	Straight
Mounting method for subbase	with through hole
Pneumatic connection, port 1	für Cartridge 15 mm
Pneumatic connection, port 5	für Cartridge 15 mm
Materials note	Conforms to RoHS
Material of connecting plate	PA-reinforced
Material cover	PA-reinforced
Material seals	NBR
Material sleeve	High alloy steel, non-corrosive
Material clip	High alloy steel, non-corrosive
Material nut	High alloy steel, non-corrosive