

Manifold sub-base VABX-A-P-BV-BH-RVBBBB

Part number: 8188465

FESTO



Data sheet

| Feature | Value |
|-----------------------------|-------------------------------|
| Max. no. of valve positions | 4 |
| Dimensions W x L x H | 50.05 mm x 104.3 mm x 43.1 mm |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 136.2 g |
| Pneumatic connection 2 | For 12 mm cartridge |
| Pneumatic connection 4 | For 12 mm cartridge |
| Note on materials | RoHS-compliant |
| Material of sub-base | PA-reinforced |
| Seals material | NBR |
| Retaining bracket material | POM |
| Clip material | High-alloy stainless steel |
| Nut material | High-alloy stainless steel |