


Limit switch box SRBK-CA5-YR90-MW-1-1WG-C2

Part number: 8191215

FESTO



Data sheet

Feature	Value
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK instructions for electrical equipment
Note on materials	RoHS-compliant
Measured variable	Position
Measuring principle	Mechanical/electrical
Sensing range	0 deg...90 deg
Ambient temperature	-20 °C...70 °C
Switching output	Contact-based (gold)
Switching element function	Toggle switch, single-pin
Max. switching output voltage DC	30 V
Max. output current DC	100 mA
Max. switching capacity DC	3 W
DC operating voltage range	0 V...30 V
Microswitch type	Omron SS-01
Electrical connection	Screw terminal
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, cable outlet	Straight
Electrical connection 1, design	Rectangular
Electrical connection 1, connection technology	Screw terminal
Electrical connection 1, number of pins/wires	10
Closable nominal conductor cross-section	0.25 mm ² ...2.5 mm ²
Cable fitting	M20x1.5
Dimensions W x L x H	119 mm x 85 mm x 89 mm
Type of mounting	On flange as per ISO 5211
Mounting position	Any
Product weight	360 g
Housing colour	Black
Housing material	PA

Feature	Value
Seals material	NBR
Shaft material	PA
Material of screws	Stainless steel
Circlip material	High-alloy stainless steel
Protective cap material	PC
Switching status indication	Optical
Position indicator	Yellow/red
Angle detection setting range	0 deg...90 deg
Storage temperature	-20 °C...50 °C
Degree of protection	IP66 IP67
Shock resistance	Shock test with severity level 1 as per FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 as per FN 942017-4 and EN 60068-2-6
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Contamination level	3