


# Servo motor EMMH-AS-88-HKA-HS-S1M-T

Part number: 8215354

**FESTO**



## Data sheet

Feature	Value
Ambient temperature	-30 °C...40 °C
Note on ambient temperature	Up to 80 °C with derating of -1.5% per degree Celsius
Max. installation height	3000 m
Information on max. installation height	with 1,000 m and longer only with derating of -1.0% per 100 m
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 100 %
Conforms to standard	IEC 60034
Thermal class according to EN 60034-1	F
Max. winding temperature	155 °C
Rating class according to EN 60034-1	S1
Temperature monitoring	Digital motor temperature transmission via EnDat® 2.2
Motor type as per EN 60034-7	IM B14 IM V18
Mounting position	Any
Degree of protection	IP69K
Concentricity, coaxiality, axial runout according to DIN SPEC 42955	N
Balancing quality	G 2.5
Detent torque	<1.0% of peak torque
Bearing lifetime, under nominal conditions	20000 h
Interface code, motor out	88C
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connection technology	M17x0.75
Electrical connection 1, number of pins/wires	15
Contamination level	2
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress (except laser marking)
LABS (PWIS) conformity	VDMA24364 zone III
For use in the food industry	Approved for direct food contact
Vibration resistance	as per EN 60068-2-6

Feature	Value
Shock resistance	as per EN 60068-2-29 15 g/11 ms as per EN 60068-2-27
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK instructions for electrical equipment
Nominal operating voltage DC	680 V
Type of winding switch	Star inside
Number of pole pairs	5
Stall torque	3.95 Nm
Nominal torque	1.9 Nm
Peak torque	14.3 Nm
Nominal rotary speed	3100 rpm
Max. rotational speed	8000 rpm
Max. mechanical speed	8000 rpm
Angular acceleration	100000 rad/s <sup>2</sup>
Motor nominal power	620 W
Continuous stall current	4.8 A
Motor nominal current	2.5 A
Peak current	16.5 A
Motor constants	0.79 Nm/A
Standstill torque constant	0.83 Nm/A
Voltage constant, phase-to-phase	55.3 mVmin
Phase-phase winding resistance	1.8 Ohm
Winding inductance phase-phase	7.1 mH
Winding longitudinal inductivity Ld (phase)	3.5 mH
Cross inductivity Lq (phase)	3.9 mH
Electric time constant	3.9 ms
Thermal time constant	62 min
Thermal resistance	1.01 K/W
Measuring flange	300 x 300 x 30 mm, steel
Rotor mass moment of inertia	2.09 kgcm <sup>2</sup>
Total output inertia moment	2.09 kgcm <sup>2</sup>
Product weight	6000 g
Permissible axial shaft load	86 N
Permissible radial shaft load	430 N
Rotor position sensor	Absolute encoder, multi-turn
Rotor position sensor for manufacturer designation	EQI 1131
Rotor position encoder for absolutely detectable revolutions	4096
Rotor position sensor interface	EnDat® 22
Rotor position sensor measuring principle	Inductive
Rotor position encoder for DC operating voltage	5 V
Rotor position encoder for DC operating voltage range	3.6 V...14 V
Rotor position encoder for positional values per revolution	524288
Rotor position sensor resolution	19 bit
Rotor position encoder system accuracy angle measurement	-120 arcsec...120 arcsec
MTTF, subcomponent	190 years, rotor position sensor