


Parallel kit
EAMM-U-86-D60-80P-102-S1-G2
Part number: 8234873

FESTO



Data sheet

Feature	Value
Size	86
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	175 kgmm ²
No-load driving torque	0.25 Nm
Transferable torque	9.5 Nm
Product weight	2320 g
Interface code, actuator	D60
Interface code, motor in	80P
Note on materials	RoHS-compliant