



Cilindar zaustavljač EFSD-20-PV-M12

Broj artikla: 2942445

FESTO



Tehnički podaci

| Svojstvo | Vrijednost |
|---|--|
| Konstruktivna struktura | Electric stopper cylinder |
| Veličina | 20 |
| Položaj ugradnje | proizvoljno |
| Prepoznavanje pozicije | s Hallovim sensorom |
| Klasa korozione otpornosti KBK | 1 - niska otpornost na koroziju |
| Temperatura okoline | -10 ... 60 °C |
| Temperatura ležaja | -20 ... 60 °C |
| Relativna vlažnost zraka | 0 - 95 % ne kondenzira se |
| Duljina prigušivanja | 11,5 mm |
| Težina proizvoda | 420 g |
| Maks. frekvencija takta | 0,33 Hz |
| Vrsta pričvršćenja | Sa setom za prilagodbu |
| Dozvola | RCM Mark |
| Materijal - napomena | RoHS sukladno |
| PWIS conformity | VDMA24364 zone III |
| Material cover | PA PA ojačan |
| Material seals | NBR |
| Material housing | Hard anodised wrought aluminium alloy |
| Material piston rod | visokolegirani čelik, nehrđajući |
| Material screws | Obloženi čelik |
| Maks. primljena struja | 2 A |
| Nazivni pogonski napon DC | 24 V |
| Dozvoljena kolebanja napona | +/- 15 % |
| Vrsta motora | Koračni motor |
| KC mark | KC-EMV |
| CE znak (vidi izjavu o sukladnosti) | prema EU-EMV-smjernici |
| UKCA marking (see declaration of conformity) | To UK instructions for EMC |
| Mehanička zaštita | IP40 |
| Maks. duljina voda | 30 m |
| Indikacija pogonske spremnosti | LED |
| Electrical connection for actuator, connection type | Utikači |
| Electrical connection for actuator, connection technology | M12x1, A-coded u skladu s EN 61076-2-101 |
| Electrical connection for actuator, number of pins/wires | 5 |
| Electrical connection for sensor, connection type | Utikači |
| Electrical connection for sensor, connection technology | M12x1, A-coded u skladu s EN 61076-2-101 |
| Electrical connection for sensor, number of pins/wires | 5 |