

Standardni cilindar DSBC-50-70-D3-PPVA-N3

Broj artikla: 3659473

FESTO

S podesivim prigušenjem na oba kraja



Tehnički podaci

Svojstvo	Vrijednost
Hod	70 mm
Promjer klipa	50 mm
Navoj klipnjače	M16x1,5
Prigušivanje	PPV: pneumatsko prigušivanje obostrano podesivo
Položaj ugradnje	proizvoljno
Odgovara normi	ISO 15552
Kraj klipnjače	Vanjski navoj
Konstruktivna struktura	Klip Klipnjača Profilna cijev
Prepoznavanje pozicije	za beskontaktni prekidač
Varijante	jednostrana klipnjača
Operating pressure MPa	0,04 ... 1,2 MPa
Pogonski tlak	0,4 ... 12 bar
Način funkcioniranja	dvoradno
Pogonski medij	Komprimirani zrak prema ISO 8573-1:2010 [7:4:4]
Uputa o mediju pogona i upravljanja	Nauljeni pogon moguć (u daljnjem pogonu potreban)
Klasa korozione otpornosti KBK	2 - umjerena otpornost na koroziju
PWIS conformity	VDMA24364-B1/B2-L
Temperatura okoline	-20 ... 80 °C
Energija naleta u krajnjim položajima	1 J
Duljina prigušivanja	22 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	990 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	1.178 N
Pokretna masa kod hoda 0 mm	365 g
Prirast pokretne mase po 10 mm hoda	25 g
Osnovna težina kod hoda 0 mm	1.216 g
Prirast težine po 10 mm hoda	78 g
Vrsta pričvršćenja	s unutarnjim navojem s priborom po izboru:
Pneumatski priključak	G1/4
Materijal - napomena	RoHS sukladno
Material cover	Die-cast aluminium, coated
Material piston seal	TPE-U(PU)
Material piston	Aluminijska legura za gnječenje
Material piston rod	visokolegirani čelik
Material piston rod wiper seal	TPE-U(PU)
Buffer seal material	TPE-U(PU)
Cushion piston material	POM
Material cylinder barrel	Smooth-anodised wrought aluminium alloy
Material nut	Čelik pocinčan
Rod wiper seal material	TPE-E
Material bearing	Metal polymer compound
Material of flange screw	Čelik pocinčan