



# ストップシリンダ EFSD-20-PV-M12

部品番号: 2942445

FESTO



## データシート

特長	値
構造	Electric stopper cylinder
サイズ	20
取付方向	任意
位置検出	ホールセンサ付
耐酸性クラス: CRC	1 - 腐食ストレス低
周囲温度	-10 ... 60 °C
保管温度	-20 ... 60 °C
相対湿度	0 - 95 % 非凝縮
クッションストローク	11.5 mm
質量	420 g
サイクル周波数	0.33 Hz
取付方法	取付金具付
認証	RCM Mark
材質	RoHS対応
PWIS conformity	VDMA24364 zone III
Material cover	PA 強化PA
Material seals	NBR
Material housing	Hard anodised wrought aluminium alloy
Material piston rod	ステンレス
Material screws	めっき鋼
最大電流補正	2 A
作動電圧 DC	24 V
許容電圧変動	+/- 15 %
モータタイプ	ステップモータ
KC mark	KC-EMV
CEマーク	EU-EMVガイドライン準拠
UKCA marking (see declaration of conformity)	To UK instructions for EMC
保護仕様	IP40
ラインの最長	30 m
ディスプレイの状態表示	LED
Electrical connection for actuator, connection type	プラグ
Electrical connection for actuator, connection technology	M12x1, Aコード ( EN 61076-2-101 )
Electrical connection for actuator, number of pins/wires	5
Electrical connection for sensor, connection type	プラグ
Electrical connection for sensor, connection technology	M12x1, Aコード ( EN 61076-2-101 )
Electrical connection for sensor, number of pins/wires	5