


Reductor EMGA-80-P-G20-EAS-80

Cod: 8141743

FESTO



Fisa tehnica

Caracteristica	valoare
Transmisie flansa	80 mm
Motor cu flansa	80 mm
Joc de rasucire	0,15 deg
tipul reductorului	Angrenaj planetar
Raport de transmisie	20:1
Viteza maxima de intrare	7.000 1/min
Temperatura de operare reductor	-25 ... 90 °C
Conformitatea PWIS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de actionare continua	120 Nm
Momentul de inertie al angrenajului	0,406 kgcm ²
Cuplu maxim iesire	240 Nm
Eficienta maxima	96 %
rigiditate la torsiune	10,4 Nm/arcmin
Greutate produs	2.500 g
Interfata reductor arbore de iesire	80G
Interfata reductor arbore de antrenare	80P
Indicatie material	conform RoHS