


IO-Link Master USB CDSU-1

Broj artikla: 8091509

FESTO



Tehnički podaci

Svojstvo	Vrijednost
Odgovara normi	EN 61131-9
Upute za korištenje	For use with the USB IO-LinkMaster Tool software (available from the Support Portal) for Windows version 7 or higher (32/64 bit).
Input voltage	5 V DC at the USB connection 24 V DC \pm 6 V via external supply
Input current	Max. 2.5 A via external supply Max. 600 mA at the USB connection
Output voltage	24 V DC \pm 10% with USB operation 24 V DC \pm 6 V with external supply (max. input voltage)
Zaštita od zamjene polova	za priključke pogonskog napona
Otpornost na kratki spoj	da
Otpornost na preopterećenje	ne postoji
Dozvola	RCM Mark
CE znak (vidi izjavu o sukladnosti)	prema EU-EMV-smjernici in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
PWIS conformity	VDMA24364 zone III
Temperatura ležaja	-10 ... 75 °C
Mehanička zaštita	IP20
Temperatura okoline	0 ... 55 °C
Težina proizvoda	106 g
Protokol	IO-Link
IO spoj, protokol	Master V 1.0 Master V 1.1
IO spoj, modus komunikacije	COM1 (4,8 kBaud), COM2 (38,4 kBaud), COM3 (230,4 kBaud)
IO spoj, tip porta	A B, with accessories
IO spoj, broj portova	1
IO spoj, širina procesnih podataka OUT	can be parameterised 0 - 32 bytes
IO spoj, širina procesnih podataka IN	can be parameterised 0 - 32 bytes
IO spoj, minimalno vrijeme ciklusa	1,5 ms
IO spoj, memorija	2 kByte / Port
IO spoj master, izlazna struja	80 mA with USB operation Max. input current with external supply
Power supply, function	Additional power supply
Napajanje, način spajanja	Utičnica
Napajanje, tehnologija spajanja	Coaxial
Power supply, note on connection technology	for plugs with outside diameter 5.5 mm/inside diameter 2.1 mm
Napajanje, broj pinova/žica	2
USB interface, connection technology	USB 2.0 type B mini
USB interface, connection pattern	00995868
USB interface, galvanic isolation	da
Electrical connection for IO-Link®, connection type	Utičnica
Electrical connection for IO-Link®, connection technology	M12x1, A-coded u skladu s EN 61076-2-101
Electrical connection for IO-Link®, number of pins/wires	5
IO-Link® electrical connection, occupied pins/wires	3
Materijal - napomena	RoHS sukladno
Material housing	Anodised wrought aluminium alloy