

Reductor EMGA-120-P-G8-SAS-100

Cod: 8141753

FESTO



Fisa tehnica

| Caracteristica | valoare |
|--|-------------------------|
| Transmisie flansa | 120 mm |
| Motor cu flansa | 100 mm |
| Joc de rasucire | 0,12 deg |
| tipul reductorului | Angrenaj planetar |
| Raport de transmisie | 8:1 |
| Viteza maxima de intrare | 6.500 1/min |
| Temperatura de operare reductor | -25 ... 90 °C |
| Conformitatea PWIS | VDMA24364-B2-L |
| Tip de protectie | IP54 |
| Cuplu de actionare continua | 120 Nm |
| Momentul de inertie al angrenajului | 1,431 kgcm ² |
| Cuplu maxim iesire | 192 Nm |
| Eficienta maxima | 97 % |
| rigiditate la torsiune | 18 Nm/arcmin |
| Greutate produs | 6.000 g |
| Interfata reductor arbore de iesire | 120G |
| Interfata reductor arbore de antrenare | 100A |
| Indicatie material | conform RoHS |